

# Genuine GD Parts – The perfect fit for maximum performance and efficiency

The vast experience and knowledge of GD's highly qualified air specialists, coupled with the use of genuine GD parts and quality consumables that are guaranteed to perform, ensures the best possible efficiency from your GD air system.

## Service Kits – all the parts you need in a single box!

Using Service Kits allows you to plan compressor maintenance in advance, avoiding surprises and missing parts for a specific service or breakdown. No more wasted time searching for and ordering separate spare parts, service kits are a cost effective maintenance solution.



## Technical data

### Simplex

Model	Nominal Pressure	Drive Motor	FAD at 8 bar g*	FAD at 10 bar g*	Noise level	Dimensions	Weight
	[bar g]	[kW]	[m <sup>3</sup> /hr]	[m <sup>3</sup> /hr]	[dB(A)]	L x W x H [mm]	[kg]
EnviroAire S4	8 / 10	4	23.6	21.2	65	1168 x 686 x 711	315
EnviroAire S6	8 / 10	5.5	34.5	26.0	70	1168 x 762 x 711	352
EnviroAire S8	8 / 10	7.5	53.0	41.3	73	1168 x 762 x 711	367

### Duplex

Model	Nominal Pressure	Drive Motor	FAD at 8 bar g*	FAD at 10 bar g*	Noise level	Dimensions	Weight
	[bar g]	[kW]	[m <sup>3</sup> /hr]	[m <sup>3</sup> /hr]	[dB(A)]	L x W x H [mm]	[kg]
EnviroAire S7D	8 / 10	7	47.2	42.5	64	1420 x 864 x 1404	562
EnviroAire S11D	8 / 10	11	69.0	52.0	68	1422 x 864 x 1397	599
EnviroAire S15D	8 / 10	15	106.0	82.6	71	1422 x 864 x 1397	615

\* Data measured and stated in accordance with ISO 1217 Edition 4, Annex C & E at the following conditions:  
Air Intake Pressure 1 bar a / 14.5 psi; Air Intake Temperature 20° C / 68° F; Humidity 0 % (dry)

\*\* Measured in free field conditions in accordance with ISO 2151, tolerance ± 3 dB (A)