ORDERING INFORMATION

MODEL	DESCRIPTION					
MODEL	DELIVERY SYSTEM CFM	FILTER GALLONS				
CTS-T15	125-250	15				
CTS-T30	250-560	30				
CTS-T55	560-1125	55				

FILTER REPLACEMENTS

PART #	DESCRIPTION			
7037093	Troubleshooter 15 gal. filter			
7037094	Troubleshooter 30 gal. filter			
7037095	Troubleshooter 55 gal. filter			

SPECIFICATIONS

Inter-connecting fittings and hoses are supplied for connecting the delivery system to the filter modules.

	MAX	CFM@	DIMENSIONS (IN)			INLET	OIL	CONTAINER	PUMP
	GPM	20 PSI	Н	D	W	NPT	OUT	MATERIAL	MATERIAL
	0.9	0.35	38	16	24	¹ / ₂ ″ (3)	3/4″	Polypro.	Acetal/ Viton

FILTER MODULE	MAX	MAX OIL CAPACITY	DIMENSIONS (IN)			INLET	WATER OUT	CONTAINER	WEIGHT
GALLONS	HP	GALLONS	н	D	W	(IN)	(IN)	MATERIAL	LBS
15	50	5	20	15	15	3⁄8	3⁄4	Polyethyl.	90
30	100	12	29	19	19	3⁄8	2	Polyethyl.	200
55	200	24	33	23	23	3⁄8	2	Polyethyl.	400

*Note: when properly maintained, the troubleshooter will have discharge water containing less than 15 ppm of oil remaining. A Troubleshooter filter module could last 12 months in a Rotary Screw application. However, filter life may be less due to lubricant, compressor type, and maintenance. Reduce cfm ratings by 50% for reciprocating compressors with lubricators. Not recommended for Food Grade or Silicone based lubricants. All design specifications are subject to change without notice.