



**COMPRESSOR DATA SHEET**

Federal Uniform Test Method for Certain Air Compressors Not Applicable

**Rotary Compressor: Variable Frequency Drive**

**MODEL DATA - FOR COMPRESSED AIR**

1	Manufacturer: <b>Gardner Denver</b>		
2	Model Number	<b>PureAir TVS160</b>	Date: <b>June 2024</b>
	<input checked="" type="checkbox"/> Air-cooled <input type="checkbox"/> Water-cooled		Type: <b>Screw</b>
	<input type="checkbox"/> Oil Injected <input checked="" type="checkbox"/> Oil-Free		# of Stages: <b>2</b>
3*	Full Load Operating Pressure <sup>b</sup>	<b>150</b>	psig <sup>b</sup>
4	Drive Motor Nominal Rating	<b>200</b>	hp
5	Drive Motor Nominal Efficiency	<b>95.3%</b>	percent
6	Fan Motor Nominal Rating (if applicable)	<b>10.1</b>	hp
7	Fan Motor Nominal Efficiency	<b>92.1%</b>	percent
8*	Input Power (kW)	Capacity (acfm) <sup>a,d</sup>	Specific Power (kW/100 acfm) <sup>d</sup>
	<b>178.0</b> Max	<b>837</b>	<b>21.27</b>
	<b>152.9</b>	<b>729</b>	<b>20.99</b>
	<b>128.6</b>	<b>617</b>	<b>20.85</b>
	<b>105.3</b>	<b>502</b>	<b>20.98</b>
	<b>83.1</b>	<b>384</b>	<b>21.63</b>
	<b>61.9</b> Min	<b>264</b>	<b>23.47</b>
9*	Total Package Input Power at Zero Flow <sup>c,d</sup>	<b>0.0</b>	kW
<p>Note: Graph is only a visual representation of the data in section 8                  Note: Y-axis scale 10 to 35, +5kW/100acfm increments if necessary above 35                  X-Axis Scale, 0 to 25% over maximum capacity</p>			

\* For models that are tested in the CAGI Performance verification Program, these items are verified by program administrator

Consult CAGI website for a list of participants in the third party verification program: [www.cagi.org](http://www.cagi.org)

NOTES:

- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; acfm is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity and Electrical Consumption were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1% manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document



Volume flow rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
m <sup>3</sup> /min	ft <sup>3</sup> /min	%	%	
Below 0.5	Below 17.6	+/-7	+/-8	+/- 10%
0.5 to 1.5	17.6 to 53	+/-6	+/-7	
1.5 to 15	53 to 529.7	+/-5	+/-6	
Above 15	Above 529.7	+/-4	+/-5	

Member:

ROT 031.2