

Gardner
Denver[®]

ROTARY COMPRESSORS | AIR TREATMENT

Total Solution Provider



Gardner Denver

provides the broadest range of air compressors that handle a wide-variety of applications. From the most demanding, requiring compressed air 24/7/365 to the fluctuating day-to-day or shift-to-shift, we have the right compressor to maximize productivity and energy savings.



FIXED SPEED | OIL-FLOODED ROTARY COMPRESSORS



hydrovane

Versatile

- 2-15 HP
- 100-150 PSIG
- 5-50 CFM



L Series

Simplistic

- 5-400 HP
- 75-190 PSIG
- 13-1604 CFM



Electra-Saver II G2

Slow Speed Reliability

- 40-300 HP
- 100-200 PSIG
- 137-1541 CFM



Electra-Saver/G2

Turn-Valve Efficiency

- 75-500 HP
- 100-200 PSIG
- 342-2459 CFM



Electra TS

Market-Leading Efficiency

- 200-300 HP
- 100-200 PSIG
- 1092-1639 CFM

VARIABLE SPEED | OIL-FLOODED ROTARY COMPRESSORS



LRS Series

Energy Efficiency

- 7-290 kW
- 75-190 PSIG
- 29-1620 CFM



Electra TSV

Ultimate Efficiency

- 150-225 kW
- 100-200 PSIG
- 1178-1652 CFM

OIL-FREE | COMPRESSORS



EnviroAire S & ES

- 3-10 HP
- 116-140 PSIG
- 8-126 CFM



EnviroAire VS

- 15-37 kW
- 75-145 PSIG
- 65-242 CFM



EnviroAire T

- 37-315 kW
- 115-145 PSIG
- 186-1705 CFM



EnviroAire TVS

- 37-315 kW
- 115-145 PSIG
- 93-1596 CFM



Ultima

- 75-160 kW
- 247-842 CFM
- 75-145 PSIG

REFRIGERATED DRYERS

RPC Series

Energy Saving

- 75-2,000 CFM
- Latest Advancement in Heat Transfer Technology

RHT/GHRN Series

High Temp

- 20-132 CFM
- Up to 180°F Inlet Temperature

RHP

High Pressure

- 30-3,000 CFM
- Up to 725 PSIG Inlet Pressure

XGNC Series

Non-Cycling

- 7-1200 CFM
- 1800-12000 CFM Modular

RGD Series

Non-Cycling

- 2.5-1200 CFM
- Air-Cooled
- 2-Year Warranty

GNC Series

Non-Cycling

- 10-650 CFM

GSRN Series

Non-Cycling

- 10-2,250 CFM
- Air-Cooled and Water-Cooled
- Stainless Steel Components

GTRC Series

Cycling Dryer

- 100-2,250 CFM
- Adjustable Dew Point
- Stainless Steel Components

XGCV Series

Cycling Dryer

- 10-24,000 CFM

DESICCANT DRYERS

DGH Series

Heatless

- 3-5,400 CFM
- Dew Point to -100°F

DHP/GEHD Series

Externally Heated

- 100-4,000 CFM
- Dew Point to -40°F

DPB/GBPD Series

Blower Purge

- 100-4,300 CFM
- Dew Point to -40°F

XGHB Series

Heated Blower

- 150-8000 CFM
- Dew Point to -40°F

DHC Series

Heat of Compression

- 350-10,000 CFM
- Dew Point Demand Control

XGHP Series

Heated Purge

- 150-8000 CFM
- Dew Point to -40°F

XGML Series

Modular Desiccant

- 3-177 CFM
- -40°F & -100°F Dew Point

XGHL Series

Heatless

- 90-5000 CFM
- Dew Point to -100°F

MEMBRANE DRYERS, NITROGEN GENERATORS, CHILLERS, FILTERS, PIPING, LUBRICANTS, & CONDENSATE MANAGEMENT

Membrane Dryers

MES/MMD Series

- 1.5-138 CFM
- Dew Point to -40°F

Filters

XG/FIL/GIL Series

- 20-21,250 CFM
- High Pressure and High Temperature Filters Available

Drains

XGDR/SMD/DS/EDDS Series

- Zero-Loss
- Electric Timed Drain

Mist Eliminators

XG/FME Series

- 125-10,000 CFM
- Mist Eliminator

Piping

Quick-Lock & Big Lock Series

- Sizes from 0.5-10"
- Extruded Aluminum Piping
- All Metal Fittings

Oil/Water Separators

GD PAK/CTS/CTS-T Series

- Effectively Treats Contaminated Condensate

Intelli-PAK

- Cabinet PAK Design
- Proprietary Tank Connections

Nitrogen Generators

XGN2 Series

- Membrane 1-153 CFM, 95-99.5% purity
- PSA 15-2353 CFM, 95-99.999% purity
- High Pressure

GDN2 Series

- 98-99.999% Purity
- Skid-Mounted PSA Design

Lubricants

AEON Lubricant

- 8,000 Hr Synthetic Blends
- Food Grade Available
- High Temperature Blends

Other

XGCHL Series - Process Chillers

- 0.5-106.0 Ton
- 113°F Ambient Standard

XGTK Series - Air Storage Tanks

- Vertical & Horizontal
- 30-5000 gal Standard

XGCT - Activated Carbon Towers

- 80-5500 CFM




The leader in every market we serve
by continuously improving all business processes
with a focus on innovation and velocity

**Gardner
Denver**[®]

1800 Gardner Expressway
Quincy, IL 62305
www.gardnerdenver.com



©2024 Industrial Technologies and Services, LLC
Printed in U.S.A.
GS-LINE 15th Ed. X/24

 Please recycle after use.