

COMPRESSOR DATA SHEET



In Accordance With Federal Uniform Test Method for Certain Lubricated Air Compressors

Rotary Compressor: Variable Frequency Drive

MODEL DATA - FOR COMPRESSED AIR				
1	Manufacturer: Gardner Denver			
2	Model Number: ETSV185-250hp-200psi	Date:	02/07/24	
	<input checked="" type="checkbox"/> Air-cooled <input type="checkbox"/> Water-cooled	Type:	Screw	
		# of Stages:	1	
3*	Full Load Operating Pressure ^b	200	psig ^b	
4	Drive Motor Nominal Rating	250	hp	
5	Drive Motor Nominal Efficiency	95.7	percent	
6	Fan Motor Nominal Rating (if applicable)	7.5	hp	
7	Fan Motor Nominal Efficiency	86.5	percent	
8*	Input Power (kW)		Capacity (acfm) ^{a,d}	Specific Power (kW/100 acfm) ^d
	240.58		1057.4	22.75
	205.70		902.7	22.79
	171.14		741.2	23.09
	138.41		577.8	23.95
	104.95		412.7	25.43
	95.97		368.7	26.03
9*	Total Package Input Power at Zero Flow ^{c, d}	25.0	kW	
10	Isentropic Efficiency	81.35	%	
11	<p align="center"> Note: Graph is only a visual representation of the data in Section 8 Note: Y-Axis Scale, 10 to 35, + 5kW/100acfm increments if necessary above 35 X-Axis Scale, 0 to 25% over maximum capacity </p>			

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator

Consult CAGI website for a list of participants in the third party verification program: www.cagi.org



- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%, manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:
NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	NO Load / Zero Flow Power
<u>m³ / min</u>	<u>ft³ / min</u>	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 031.1