



VALUE PLUS | 15 HP RECIPROCATING COMPRESSORS

Pump Model VP60

The Solution to Your Application

The Value Plus compressor line was engineered for industrial applications that require an electric driven compressor. Each compressor was designed with top quality bearings, cast iron cylinders and vibration-free compressor pumps to ensure longevity of the compressor package. The Value Plus is another quality product in the Gardner Denver line of air compressors.

Standard Features

- Magnetic starters
- Automatic start/stop operation
- OSHA approved belt guard
- NEMA rated electric motors
- ASME coded air receivers
- Manual tank drain
- 0-300 PSIG air pressure gauge on receiver
- Preset pressure switch
- Available voltages - 208/230/460
- 1-Year package warranty
- 1-Year pump warranty

Available Options

- Vibration isolators

Gardner

Denver

BARE PUMP

| MODEL | APPROX. SHIP WEIGHT (LBS) | BORE INCHES | STROKE INCHES | STAGE # | # OF CYLINDERS | DIAM. FLYWHEEL INCHES | DIAM. PULLEY INCHES | OIL CAPACITY QTS. | MAX PUMP RPM |
|-------|---------------------------|-------------|---------------|---------|----------------|-----------------------|---------------------|-------------------|--------------|
| VP60 | 264 | 4.7 × 4.7 | 3.3 | 2 | 3 | 19.7 | 11.35 | 1.6 | 1065 |

SIMPLEX TANK MOUNTED UNITS

| MOTOR HP | TANK CAPACITY GAL. | VALUE PLUS CDSVPA | DIMENSIONS L × W × H INCHES | APPROX. SHIP WEIGHT LBS. | VOLTAGE | PHASE | CFM DELIVERY @ 175 PSI | TANK OUTLET |
|----------|--------------------|-------------------|-----------------------------|--------------------------|-------------|-------|------------------------|-------------|
| 15 | 120 | 15H120E | 72 × 30 × 54 | 935 | 208/230/460 | 3 | 44.4 | 1.25" NPT |

Gardner Denver®

Gardner Denver, Inc.

1800 Gardner Expressway
Quincy, IL 62305
866-440-6241

www.gardnerdenver.com/gdproducts



©2018 Gardner Denver, Inc. Printed in U.S.A.
GRCS-VP-VP60 1st Ed. 2/18

