



COMPRESSOR DATA SHEET

Federal Uniform Test Method for Certain Air Compressors Not Applicable

Rotary Compressor: Variable Frequency Drive

MODEL DATA - FOR COMPRESSED AIR

1	Manufacturer: Gardner Denver			
2	Model Number	PureAir TVS160	Date: June 2024	
	<input checked="" type="checkbox"/> Air-cooled <input type="checkbox"/> Water-cooled		Type: Screw	
	<input type="checkbox"/> Oil Injected <input checked="" type="checkbox"/> Oil-Free		# of Stages: 2	
3*	Full Load Operating Pressure ^b	100	psig ^b	
4	Drive Motor Nominal Rating	200	hp	
5	Drive Motor Nominal Efficiency	95.3%	percent	
6	Fan Motor Nominal Rating (if applicable)	10.1	hp	
7	Fan Motor Nominal Efficiency	92.1%	percent	
8*	Input Power (kW)		Capacity (acfm) ^{a,d}	Specific Power (kW/100 acfm) ^d
	166.4	Max	899	18.51
	140.5		782	17.98
	115.7		659	17.55
	92.2		532	17.32
	70.1		401	17.49
	49.7	Min	267	18.62
9*	Total Package Input Power at Zero Flow ^{c,d}		0.0	kW
<p>Note: Graph is only a visual representation of the data in section 8 Note: Y-axis scale 10 to 35, +5kW/100acfm increments if necessary above 35 X-Axis Scale, 0 to 25% over maximum capacity</p>				

* For models that are tested in the CAGI Performance verification Program, these items are verified by program administrator

Consult CAGI website for a list of participants in the third party verification program: www.cagi.org

NOTES:

- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; acfm is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity and Electrical Consumption were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1% manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document



Volume flow rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
m ³ /min	ft ³ /min	%	%	
Below 0.5	Below 17.6	+/-7	+/-8	+/- 10%
0.5 to 1.5	17.6 to 53	+/-6	+/-7	
1.5 to 15	53 to 529.7	+/-5	+/-6	
Above 15	Above 529.7	+/-4	+/-5	

Member:

ROT 031.2