

Model Number	Flow Rating SCFM @ 100 psig (7 bar)	Dimensions		Connections		Weight lbs (kg)
		A	B	In/Out	Drain	
FSG20*	20	3.75" (95 mm)	7.87" (200 mm)	1/2"	1/2"	2.5 (1,1)
FSG40*	40	3.75" (95 mm)	7.87" (200 mm)	1/2"	1/2"	2.5 (1,1)
FSG60*	60	3.75" (95 mm)	9.00" (230 mm)	3/4"	1/2"	2.5 (1,1)
FSG80*	80	3.75" (95 mm)	9.00" (230 mm)	3/4"	1/2"	2.5 (1,1)
FSG130*	130	3.75" (95 mm)	10.63" (270 mm)	3/4"	1/2"	3.0 (1,4)
FSG160*	160	5.50" (140 mm)	10.24" (260 mm)	1 1/2"	1/2"	5.5 (2,5)
FSG215*	215	5.50" (140 mm)	12.60" (320 mm)	1 1/2"	1/2"	6.0 (2,7)
FSG350*	350	5.75" (146 mm)	16.00" (406 mm)	1 1/2"	1/2"	6.9 (3,1)

\*Fill in the appropriate element code (G,P,C,V) to model number. Maximum pressure is 230 psig (16 bar). Maximum temperature is 140° F (60° C).

G=5.0 micron; Bulk Liquid/Particulate P=1.0 micron; Course Coalescing/Particulate C=0.01 micron; Coalescing V=Vapor (Charcoal)