

COMPRESSOR DATA SHEET



In Accordance With Federal Uniform Test Method for Certain Lubricated Air Compressors

Rotary Compressor: Variable Frequency Drive

MODEL DATA - FOR COMPRESSED AIR				
1	Manufacturer: Gardner Denver			
2	Model Number: L15RS-20hp-130psi		Date:	08/28/23
	<input checked="" type="checkbox"/> Air-cooled	<input type="checkbox"/> Water-cooled	Type:	Screw
			# of Stages:	1
3*	Full Load Operating Pressure ^b		130	psig ^b
4	Drive Motor Nominal Rating		20	hp
5	Drive Motor Nominal Efficiency		91.0	percent
6	Fan Motor Nominal Rating (if applicable)		NA	hp
7	Fan Motor Nominal Efficiency		NA	percent
8*	Input Power (kW)		Capacity (acfm) ^{a,d}	Specific Power (kW/100 acfm) ^d
	18.65		79.7	23.39
	15.87		67.1	23.65
	14.07		58.6	24.01
	11.48		45.7	25.10
	9.01		32.7	27.54
	8.73		31.2	28.00
9*	Total Package Input Power at Zero Flow ^{c, d}		2.7	kW
10	Isentropic Efficiency		61.92	%
11	<p style="text-align: center;"> Note: Graph is only a visual representation of the data in Section 8 Note: Y-Axis Scale, 10 to 35, + 5kW/100acfm increments if necessary above 35 X-Axis Scale, 0 to 25% over maximum capacity </p>			

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator
 Consult CAGI website for a list of participants in the third party verification program: www.cagi.org



- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%, manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:
 NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	Zero Flow Power
m ³ / min	ft ³ / min	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 031.1

12/19 Rev 3 This form was developed by the Compressed Air and Gas Institute for the use of its members participating in the PVP. CAGI has not independently verified the reported data.