

**Gardner**  
**Denver**<sup>®</sup>

DRY BULK, CHEMICAL, HYDRAULIC & SANITARY EQUIPMENT

# Mobile/Transport Products



Gardner Denver is the only supplier to the industry that meets all your dry bulk, chemical, hydraulic and sanitary equipment needs.

Our product lines represent a proven history and reputation for quality, dependability and performance. With 150 years of manufacturing experience, Gardner Denver is a recognized leader providing compressed air and gas, vacuum and fluid transfer technologies to industries throughout the world.

## DRY BULK



**CycloBlower  
Transport Series**

HELICAL SCREW


- Airflow to 1,060 cfm
- Pressure to 18 psig
- 20 psig intermittent
- Vacuum to 17 inHg
- Weights as low as 275 lbs



**DuroFlow  
Transport Series**

ROTARY LOBE

- Airflow to 1,000 cfm
- Pressure to 15 psig
- Vacuum to 15 inHg
- Weight to 545 lbs.



**Drum  
D807/D907**

DRUM LOBE

- Airflow to 1,300 cfm
- Pressure to 20 psig
- Vacuum to 17 inHg
- Weight to 370 lbs.



**Drum  
HPD450/E490**

DRUM VANE

- Airflow to 325 cfm
- Pressure to 30 psig
- Weight to 331 lbs.



**CycloSaver**

ROTARY SCREW

- Airflow to 655 cfm
- Pressure to 36 psig
- Weight to 257 lbs.

## LIQUID BULK



**GD360**

LIQUID BULK PACKAGE

- Industry's premier bolt-&-go package
- Includes GD70 compressor, product pump & hydraulic cooler
- Auxiliary option available



**Drum  
GD150/GD175**

RADIAL VANE

- Airflow to 75 cfm
- Speed to 1800 rpm
- Pressure to 36 psig
- Weight to 125 lbs.



**GD70**

RECIP COMPRESSOR


- Airflow up to 40 CFM
- Pressure up to 40 psi
- Weight: 80 lbs



**STP 125**

TRI-LOBE

- Stainless steel food & chemical pump
- Airflow to 232 gpm
- Pressure to 140 psig
- Weight to 145 lbs.



**Drum  
SC200**

ROTARY SCREW

- Airflow to 112 cfm
- Pressure to 36 psig
- Weight to 100 lbs.



## HYDRAULIC



### MH Series

HYDRAULIC DRIVE COOLING SYSTEM

- Flow rate to 60 gpm
- Pressure rated to 3500 psig
- Stainless steel construction




### MHX Series

HYDRAULIC DRIVE COOLING SYSTEM

- Flow rate to 30 gpm
- Pressure rated to 5000 psig
- Stainless steel construction

## MOBILE VACUUM



### WITTIG TRANSPORT SERIES

#### RFL 60-102

RADIAL VANE

- Airflow to 377 cfm
- Pressure to 29 psig
- Vacuum to 24 inHg



#### RFW 150-260

RADIAL VANE

- Airflow to 906 cfm
- Pressure to 29 psig
- Vacuum to 24 inHg



### Aqualine

LIQUID RING

- Airflow to 1803 cfm
- Pressure to 22 psig
- Vacuum to 27 inHg

The leader in every market we serve  
by continuously improving all business processes  
with a focus on innovation and velocity

**Gardner  
Denver®**

[www.GardnerDenver.com](http://www.GardnerDenver.com)

©2024 Industrial Technologies and Services, LLC  
Printed in U.S.A.  
GDT-MP-LINE 4th Ed. 4/24

