



**COMPRESSOR DATA SHEET**  
**Federal Uniform Test Method for Certain Air Compressors Not Applicable**  
**Rotary Compressor: Fixed Speed**

MODEL DATA - FOR COMPRESSED AIR			
1	Manufacturer: <b>Gardner Denver</b>		
2	Model Number	<b>PureAir T90-W125 (NA-IP55)</b>	Date: <b>August 2024</b>
	<input type="checkbox"/> Air-cooled <input checked="" type="checkbox"/> Water-cooled		Type: <b>Screw</b>
	<input type="checkbox"/> Oil Injected <input checked="" type="checkbox"/> Oil-Free		# of Stages: <b>2</b>
3*	Rated Capacity at Full Load Operating Pressure a, e	<b>605</b>	acfm <sup>a, e</sup>
4	Full Load Operating Pressure <sup>b</sup>	<b>115</b>	psig <sup>b</sup>
5	Maximum Full Flow Operating Pressure <sup>c</sup>	<b>125</b>	psig <sup>c</sup>
6	Drive Motor Nominal Rating	<b>125</b>	hp
7	Drive Motor Nominal Efficiency	<b>95.0%</b>	percent
8	Fan Motor Nominal Rating (if applicable)	<b>1.2</b>	hp
9	Fan Motor Nominal Efficiency	<b>82.5%</b>	percent
10*	Total Package Input Power at Zero Flow <sup>e</sup>	<b>20</b>	kW <sup>e</sup>
11	Total Package Input Power at Rated Capacity and Full Load Operating Pressure <sup>d</sup>	<b>108.8</b>	kW <sup>d</sup>
12*	Specific Package Input Power at Rated Capacity and Full Load Operating Pressure <sup>e</sup>	<b>17.98</b>	kW/100 cfm <sup>e</sup>

\* For models that are tested in the CAGI Performance Verification Program, these are the items verified by the third party program administrator. Consult CAGI website for a list of participants in the third party verification program: [www.cagi.org](http://www.cagi.org)

NOTES:

Member:



- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex C; ACFM is actual cubic feet per minute at inlet conditions.
  - b. The operating pressure at which the Capacity (item 3) and Electrical Consumption (item 11) were measured for this data sheet.
  - c. Maximum pressure attainable at full flow, usually the unload pressure setting for load/no load control or the maximum pressure attainable before capacity control begins. May require additional power
  - d. Total package input power at other than reported operating points will vary with control strategy.
  - e. Tolerance is specified in ISO 1217, Annex C, as shown in table below.
- NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Volume Flow Rate at specified conditions		Volume Flow Rate <sup>f</sup>	Specific Energy <sup>g</sup> Consumption	No Load / Zero Flow Power <sup>e</sup>
m <sup>3</sup> / min	ft <sup>3</sup> / min			
Below 0.5	Below 17.6	+/- 7	+/- 8	+/- 10%
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 030.2