



**COMPRESSOR DATA SHEET**

Federal Uniform Test Method for Certain Air Compressors Not Applicable

**Rotary Compressor: Variable Frequency Drive**

**MODEL DATA - FOR COMPRESSED AIR**

1	Manufacturer: <b>Gardner Denver</b>		
2	Model Number	<b>PureAir TVS132-W150 (NA-IP55)</b>	Date: <b>August 2024</b>
	<input type="checkbox"/> Air-cooled	<input checked="" type="checkbox"/> Water-cooled	Type: <b>Screw</b>
	<input type="checkbox"/> Oil Injected	<input checked="" type="checkbox"/> Oil-Free	# of Stages: <b>2</b>
3*	Full Load Operating Pressure <sup>b</sup>	<b>150</b>	psig <sup>b</sup>
4	Drive Motor Nominal Rating	<b>175</b>	hp
5	Drive Motor Nominal Efficiency	<b>95.4%</b>	percent
6	Fan Motor Nominal Rating (if applicable)	<b>1.2</b>	hp
7	Fan Motor Nominal Efficiency	<b>82.5%</b>	percent
8*	Input Power (kW)	Capacity (acfm) <sup>a,d</sup>	Specific Power (kW/100 acfm) <sup>d</sup>
	<b>161.5</b>	Max	<b>772</b>
	<b>140.4</b>		<b>675</b>
	<b>119.9</b>		<b>576</b>
	<b>99.9</b>		<b>474</b>
	<b>80.7</b>		<b>370</b>
	<b>62.3</b>	Min	<b>264</b>
9*	Total Package Input Power at Zero Flow <sup>c,d</sup>		<b>0.0</b> kW

  

Note: Graph is only a visual representation of the data in section 8  
 Note: Y-axis scale 10 to 35, +5kW/100acfm increments if necessary above 35  
 X-Axis Scale, 0 to 25% over maximum capacity

\* For models that are tested in the CAGI Performance verification Program, these items are verified by program administrator

Consult CAGI website for a list of participants in the third party verification program:

[www.cagi.org](http://www.cagi.org)

NOTES:

- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; acfm is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity and Electrical Consumption were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1% manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document

Volume flow rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
m <sup>3</sup> /min	ft <sup>3</sup> /min	%	%	
Below 0.5	Below 17.6	+/-7	+/-8	+/- 10%
0.5 to 1.5	17.6 to 53	+/-6	+/-7	
1.5 to 15	53 to 529.7	+/-5	+/-6	
Above 15	Above 529.7	+/-4	+/-5	

Member:



Member:

ROT 031.2