



7-11 KW VARIABLE SPEED ROTARY SCREW COMPRESSORS

LRS-Series

Advanced Technology. Inspired Simplicity.

LRS-Series compressors from Gardner Denver feature more than just the latest compressor technology. They contain the cleanest, simplest, most intuitive machine layouts on the market. Equipped with standard TEFC main motors, robust and high performing Yaskawa inverter drives, GD Pilot™ microprocessor controllers and quiet enclosures, an LRS-Series unit from Gardner Denver is the optimal solution when a feature-rich, simple-to-operate compressor is required.

First Class Serviceability

The LRS-Series units set a new standard in serviceability. By utilizing integrated airend design techniques, Gardner Denver delivers unprecedented access to service items such as; a high efficiency air filter, air/oil separator and oil filter. At the same time, the compact design eliminates unneeded connections and minimizes piping; reducing the opportunity for leaks. Couple these features with standard automatic belt tensioning and you have a world class small horsepower compressor package.

Configuration Flexibility

LRS-Series compressors are available in base mount or AirStation™ configurations. The plug-and-play AirStation™ configuration is an LRS-Series compressor mounted on a horizontal receiver tank with or without a refrigerated air dryer. Featuring standard high-end and optional components such as a three-way bypass valve, stainless steel piping, integrated fork lift slots and an automatic tank drain, the LRS-Series AirStation™ is the ideal solution for a compressed air system that requires minimal installation time and cost.

Gardner
Denver®

L07RS-L11RS ROTARY SCREW COMPRESSOR

MODEL	DRIVE MOTOR		50 Hz				60 Hz				NOISE LEVEL ²	WEIGHT		DIMENSIONS L x W x H
	HP	KW	NOMINAL PRESSURE		FAD		NOMINAL PRESSURE		FAD ¹			DB(A)	LBS	
			PSIG	BAR	ACFM	M ³ /MIN	PSIG	BAR	ACFM	M ³ /MIN				
L07RS	10	7	100	7.0	44.5	1.26	110	7.0	42.9	1.22	63	489	222	27 x 25 x 41 (686 x 635 x 1041)
			130	9.0	35.7	1.01	130	9.0	37.6	1.07				
			190	13.0	29.3	0.83	190	13.0	27.9	0.79				
L11RS	15	11	100	7.0	63.9	1.81	110	7.0	62.1	1.76	64	509	231	
			130	9.0	55.1	1.56	130	9.0	56.9	1.61				
			190	13.0	44.5	1.26	190	13.0	43.5	1.23				

1) Data measured and stated in accordance with ISO1217, Ed. 4, Annex C & Annex E at the following conditions:

Air Intake Pressure 1 bar A, Air Intake Temperature 20° C, Humidity 0% (Dry)

2) Measured in free field conditions in accordance with ISO 2151, tolerance +/- 3 dB

AIR STATION SPECIFICATIONS, 60 HZ

MODEL	DRYER MODEL	RECEIVER SIZE GAL (LITERS)	REFRIGERANT	WEIGHT LBS (KG)	DIMENSIONS L x W x H IN. (MM)
				120 GAL	120 GAL
L07RS	GSRN XGNC	80, 120, 240 (303, 454, 908)	R134A	less dryer 984 (446) with GSRN dryer 1121 (508) with XGNC dryer 1072 (486)	less dryer 73 x 32 x 66 (1854 x 819 x 1676)
L11RS	GSRN XGNC			less dryer 984 (446) with GSRN dryer 1128 (512) with XGNC dryer 1078 (489)	with dryer 72 x 32 x 66 (1829 x 819 x 1676)

Dryer on AirStation™ package has separate electrical connection and voltage.

LRS-Series Features (7-11 kW)

- Belt drive, oil flooded, single stage rotary screw air compressor
- AEON 4000 lubricant
- Air-cooled only
- Robust inverter drive
- Optional automatic zero-loss condensate drain (with receiver tank selection)
- CRN and ASME rated aftercooler
- Optional EMI filter and standard DC bus choke
- GD Pilot™ microprocessor controller
- Integrated thermostatic thermal mixing valve
- Integrated spin-on oil filter, spin-on air/oil separator and two-stage air filter
- IP54 electrical enclosure
- Moisture separator (shipped loose)
- Optional ASME receiver tank (80, 120, 240 gallons)
- Optional line reactor (shipped loose)
- Optional mounted cycling or non-cycling refrigerated dryer (with receiver tank selection)
- Quiet enclosure
- Standard manual tank drain (with receiver tank)
- TEFC main motor
- Optional three-way bypass valve (with receiver tank and mounted dryer)
- Second pressure band control for lead/lag operation
- Stainless steel piping (with receiver tank and mounted dryer)
- UL labeled electronics (including C-UL-US open industrial control panel)
- Voltage: 230/380/400/460/575V

**Gardner
Denver®**

1800 Gardner Expressway
Quincy, IL 62305
www.gardnerdenver.com



©2024 Industrial Technologies and Services, LLC
Printed in U.S.A.
GSCS-L07RS-L11RS 1st Ed. 6/24
Supersedes GSCS-L07RS-L22RS 5th Ed. 10/22

Please recycle after use.