



VALUE PLUS | 5-8 HP RECIPROCATING COMPRESSORS

Pump Model VP20

The Solution to Your Application

The Value Plus compressor line was engineered for industrial applications that require an electric driven compressor. Each compressor was designed with top quality bearings, cast iron cylinders and vibration-free compressor pumps to ensure longevity of the compressor package. The Value Plus is another quality product in the Gardner Denver line of air compressors.

Standard Features

- Magnetic starters
- Automatic start/stop operation
- OSHA approved belt guard
- NEMA rated electric motors
- ASME coded air receivers
- Manual tank drain
- 0-300 PSIG air pressure gauge on receiver
- Preset pressure switch
- Available voltages - 208/230/460
- 1-Year package warranty
- 1-Year pump warranty

Available Options

- Vibration isolators

Gardner

Denver

BARE PUMP

MODEL	APPROX. SHIP WEIGHT (LBS)	BORE INCHES	STROKE INCHES	STAGE #	# OF CYLINDERS	DIAM. FLYWHEEL INCHES	DIAM. PULLEY INCHES	OIL CAPACITY QTS.	MAX PUMP RPM
VP20	95	3.5 × 2	3.4	2	2	16.54	9.75	1	1050

SIMPLEX TANK MOUNTED UNITS

MOTOR HP	TANK CAPACITY GAL.	VALUE PLUS CDSVPA	DIMENSIONS L × W × H INCHES	APPROX. SHIP WEIGHT LBS.	VOLTAGE	PHASE	CFM DELIVERY @ 175 PSI	TANK OUTLET
5	60	5V60E	30 × 20 × 65.5	535	230	1	15.9	.5" NPT
5	80	5H80E	66.5 × 21 × 39.5	625	230	1	15.9	.5" NPT
5	80	5H80E	66.5 × 21 × 39.5	625	208/230/460	3	15.9	.5" NPT
5	80	5V80E	33.75 × 24.5 × 69	535	230	1	15.9	.5" NPT
5	80	5V80E	33.75 × 24.5 × 69	535	208/230/460	3	15.9	.5" NPT

Gardner Denver®

Gardner Denver, Inc.

1800 Gardner Expressway
Quincy, IL 62305
866-440-6241

www.gardnerdenver.com/gdproducts



©2018 Gardner Denver, Inc. Printed in U.S.A.
GRCS-VP-VP20 1st Ed. 2/18

